



Fuelequip.com
Fax (305) 471 - 0773
E-mail: sales@fuelequip.com
E-mail: joe@apsaviation.com
Web: http://www.fuelequip.com/



sales@fuelequip.com


PLASTIC MONITORS
COLOR RATING MEMBRANES
MATCHED-WEIGHT MEMBRANES

APPROVED FOR TESTING JET
FUEL PER ASTM METHODS
D2276/IP216 AND D5452

Our 37mm, 0.8 µm (micrometer) membranes are produced in exact accordance with ASTM Research Report D1012 under which they have been granted approval for use in methods D2276 as well as IP216. We manufacture our own plastic monitors using Tenite, a product of Eastman Chemical Co. Our monitors are made to fit all recognized brands of holders including the MiniMonitor Kit and the Millipore Corp. XX64-037-30. Refill membranes are packaged with a blue paper separator

between each one to aid in separation. Matched-weight refill membranes are packaged with each pair in a glassine envelope. Each pair is matched in weight within 100µg (micrograms) in a closely controlled atmosphere. Support pads are 34mm in diameter so as to fit into the recess of the plastic monitor beneath the membrane. Matched -weight monitors have yellow plastic plugs in the inlet port and a red plug in the outlet. Single membrane monitors,

TYPE	MODEL NUMBER	MILLIPORE P/N	INTERCHANGABLE WITH ALL MEMBRANES 0.8 MICRON	DESCRIPTION
SINGLE MEMBRANE MONITORS		1985	MAWP-037-PO	48 PLASTIC MONITORS. EACH WITH A MEMBRANE AND A SUPPORT PAD
MATCHED-WEIGHT MONITORS		1986	MAWP-037-PM	48 PLASTIC MONITORS. EACH WITH A PAIR OF MEMBRANES AND A SUPPORT PAD
SINGLE MEMBRANE REFILLS		1983	AAWP-037-PO	100 MEMBRANES AND 100 SUPPORT PADS
MATCHED-WEIGHT REFILLS		1984	AAWP-037-PM	50 MATCHED-WEIGHT PAIRS OF MEMBRANES AND 50 SUPPORT PADS



MEMBRANE FILING NOTEBOOK AND PAGES

Black 3-ring leatherette notebook holds membrane filing pages. Pages made of heavy manila board, each with pockets to hold 21 mini-envelopes (see below).

NOTEBOOK FILING PAGES

packet contains ten (10) sheets - minimum order



MINI-ENVELOPES

These mini-envelopes are zip-lock polyfilm bags made to insure protection and preservation of filter membranes. Specially prepared white panel for writing data regarding the test such as date, rating, location, etc.

MINI-ENVELOPES

packet of five hundred (500) envelopes



TWEEZERS

Our tweezers have blunt points and a slip-lock device. They grip and hold membranes without needing to be held tight in your hand.

TWEEZERS



47MM MEMBRANES

We have these filter membranes in stock. They are intended for testing jet fuel for particulate content in accordance with ASTM Method D5452. The membranes are white and will fit all brands and models of filter holders that accept 47mm membranes.

MEMBRANES:

- package of 100 membranes, 0.65 μ m
- package of 100 membranes, 0.8 μ m